



## Innovative hand-held microscope for mobile applications with immediate display of the image on a smartphone or tablet




















### Features

- The digital WLAN hand-held microscope is designed for rapid and simple surface observations. Ideally suited for coins, bank notes, stamps, circuit boards, plants, insects, gems and skin samples for industrial use, for all hobby scientists, children and students
- The KERN ODC 910 WLAN microscope has been specially developed for direct connection to your WLAN-enabled smartphone or tablet with iOS or android
- During the live transfer to your smartphone or tablet you can take photos and videos of the sample you are investigating, and these can also be stored on your device. For larger videos you can also insert a mini SD card directly into the microscope
- With the WLAN microscope you can easily adjust the magnification to suit all conventional samples. The focus can be adjusted to a magnification of 10× as well as 200×
- The six LEDs fitted in a ring shape ensure strong and effective illumination of your sample. Use the adjustment wheel on the microscope to control the illumination setting.
- You can download the app for the ODC 910 WLAN microscope from the Apple App Store or the Android Google Play Store free of charge and this app enables you to directly transfer images and videos from the microscope to your smartphone or tablet through a simple connection
- The scope of delivery includes the WLAN microscope with integrated rechargeable battery pack, a flexible column which is easy to adjust and which has a swan neck so that you can achieve the ideal height setting, as well as a mains adapter

#### STANDARD



Model	Resolution	Interface	FPS	Sensor	Sensor size	Supported operating system	Magnification levels	Focusing stand	Illumination	
<b>KERN</b>										
<b>ODC 910</b>	2 MP	WLAN, SD	15 – 30	CMOS	1/4"	Android, iOS	10×, 200×	Goose neck	6× LED	

 360°	<b>360° rotatable microscope head</b>	 FL-LED	<b>Fluorescence illumination for compound microscopes</b> With 3 W LED illumination and filter	 WLAN	<b>WLAN data interface:</b> For transmitting of the picture to a mobile display device
 MONO	<b>Monocular Microscope</b> For the inspection with one eye	 PH	<b>Phase contrast unit</b> For a higher contrast	 HDMI	<b>HDMI digital camera</b> For direct transmitting of the picture to a display device
 BINO	<b>Binocular Microscope</b> For the inspection with both eyes	 DF	<b>Darkfield condenser/unit</b> For a higher contrast due to indirect illumination	 SOFTWARE	<b>PC software</b> To transfer the measurements from the device to a PC.
 TRINO	<b>Trinocular Microscope</b> For the inspection with both eyes and the additional option for the connection of a camera	 POLAR	<b>Polarising unit</b> To polarise the light	 AUTO ATC	<b>Automatic temperature compensation</b> For measurements between 10 °C and 30 °C
 ABBE	<b>Abbe Condenser</b> With high numerical aperture for the concentration and the focusing of light	 INFINITY	<b>Infinity system</b> Infinity corrected optical system	 IP	<b>Protection against dust and water splashes IPxx</b> The type of protection is shown by the pictogram.
 HAL	<b>Halogen illumination</b> For pictures bright and rich in contrast	 ZOOM	<b>Zoom magnification</b> For stereomicroscopes	 BATT	<b>Battery operation</b> Ready for battery operation. The battery type is specified for each device.
 LED	<b>LED illumination</b> Cold, energy saving and especially long-life illumination	 PARALLEL	<b>Parallel optical system</b> For stereomicroscopes, enables fatigue-proof working	 RECHARGE	<b>Battery operation rechargeable</b> Prepared for a rechargeable battery operation
 IL	<b>Incident illumination</b> For non-transparent objects	 SCALE	<b>Integrated scale</b> In the eyepiece	 230 V	<b>Mains adapter</b> 230V/50Hz in standard version for EU. On request GB, AUS or USA version.
 TL	<b>Transmitting illumination</b> For transparent objects	 SD	<b>SD card</b> For data storage	 230 V	<b>Power supply</b> Integrated in balance. 230V/50Hz standard EU. More standards e.g. GB, AUS or USA on request.
 FL	<b>Fluorescence illumination</b> For stereomicroscopes	 USB 2.0	<b>USB 2.0 digital camera</b> For direct transmitting of the picture to a PC	 1 DAY	<b>Package shipment</b> The time required to manufacture the product internally is shown in days in the pictogram.
 FL-HBO	<b>Fluorescence illumination for compound microscopes</b> With 100 W mercury lamp and filter	 USB 3.0	<b>USB 3.0 digital camera</b> For direct transmitting of the picture to a PC		

## Abbreviations

<b>C-Mount</b> Adapter for the connection of a camera to a trinocular microscope	<b>LWD</b> Long Working Distance	<b>SWF</b> Super Wide Field (Field number at least $\varnothing$ 23 mm for 10 $\times$ eyepiece)
<b>FPS</b> Frames per second	<b>N.A.</b> Numerical Aperture	<b>W.D.</b> Working Distance
<b>H(S)WF</b> High (Super) Wide Field (Eyepiece with high eye point for wearers of glasses)	<b>SLR Kamera</b> Single-Lens Reflex camera	<b>WF</b> Wide Field (Field number up to $\varnothing$ 22 mm for 10 $\times$ eyepiece)

## Your KERN specialist dealer: